

ECOSOFT MO2 8" REVERSE OSMOSIS SYSTEM

CODE IRIM: EEOSPMQM02C00

APPLICATIONS

Process water, rinse water, steam boilers, heating and cooling circuits, agriculture, desalination, food and beverage, utility water treatment.

EQUIPMENT:

- Grundfos® CR 5-20 high pressure pump...1 pcs
- 8040 membrane housing 2 pcs
- BB20 sediment prefilter 2 pcs
- Motorized valves 2 pcs
(feed water in, flush out)
- Balancing valves 2 pcs
(concentrate reject, concentrate recycle)
- Electrical cabinet with Ecosoft controller...1 set
- Piping, instrumentation, steel frame 1 set

OPTIONS

- Filmtec™ XLE-440 / ECO PRO-440 or Ecosoft ELP-8040 membranes
- Dosing pump for antiscalant or other RO chemicals
- Permeate inlet for permeate membrane rinse
- Raw water mixing line



Ecosoft reserves the right to amend the product's system architecture provided that its functionality and usability will not deteriorate

CONNECTION PORT SIZES:

Influent water	G 1½"
Permeate	G 1"
Concentrate	G 1½"
CIP inlet	G 1½"
CIP return	G 1½"
CIP permeate	G ½"
Antiscalant dosing port	G ½"

PHYSICAL PARAMETERS:

Approximate dimensions (bare)	1.90 × 1.10 × 1.95 m (Width × Depth × Height, ±5%)
Approximate dimensions (crated)	2.10 × 1.20 × 2.22 m (Width × Depth × Height, ±5%)
Approximate weight (bare)	300 kg
Approximate weight (crated)	390 kg

ECOSOFT MO2 8" REVERSE OSMOSIS SYSTEM

Code	Product	Flow capacity, m³/h (GPH)	Membranes**
MO2TP5	Ecosoft MO2 RO System	2–2.5 (530–660)	2/80 x 40

** Membranes are not included


TECHNICAL SPECIFICATION

Permeate capacity ¹	2 m³/h
Permeate recovery ²	75%
Maximum TDS	3000 mg/L
Influent flow demand	2.7...4 m³/h (service) 10 m³/h (rinse)
Operating pressure	8...12 bar
Maximum pressure	14 bar
Electrical requirements	380...400 V, 50 Hz (3 ph)
Electrical power	3 kW
Prefilter rating	5 µm

¹ depends on feed water TDS, temperature, and permeate recovery
— see graph on the right

² for low scaling/fouling water

ECOSOFT MO2 RO FLOW CAPACITY GRAPH (WITH XLE-440 MEMBRANES)




Permeate flow rates are calculated under the following conditions:

- 2 bar influent water pressure
- 0 bar backpressure in the permeate line
- fresh membranes
- XLE-440 membrane

PIPES AND INSTRUMENTS DIAGRAM

Ecosoft MO2TP5
Reverse Osmosis System
Piping and Instrumentation Diagram



PIPE SPECIFICATIONS

01	PVC pipe	50 mm O.D.
02	PVC pipe	32 mm O.D.
03	PE hose	1/4" O.D.

VALVE AND INSTRUMENT SPECIFICATIONS

	Ball Valve		Regulating Valve		Motorized Valve		Pressure gauge (panel mount)		Rotameter
	Globe Valve		Check Valve		Pressure switch (panel mount)		Conductivity probe (process mount)		