

ECOSOFT MO4 8" REVERSE OSMOSIS SYSTEM

CODE IRIM: EEOSPMQM04C00

APPLICATIONS

Process water, rinse water, steam boilers, heating and cooling circuits, agriculture, desalination, food and beverage, utility water treatment.

EQUIPMENT:

- Grundfos® CR 10-12 high pressure pump 1 pcs
- 8040-2 membrane housing 2 pcs
- BB20 sediment prefilter 3 pcs
- Motorized valves 2 pcs
(feed water in, flush out)
- Balancing valves 2 pcs
(concentrate reject, concentrate recycle)
- Electrical cabinet with Ecosoft controller 1 set
- Piping, instrumentation, steel frame 1 set



Ecosoft reserves the right to amend the product's system architecture provided that its functionality and usability will not deteriorate

OPTIONS

- Filmtec™ XLE-440 / ECO PRO-440 or Ecosoft ELP-8040 membranes
- Dosing pump for antiscalant or other RO chemicals
- Permeate inlet for permeate membrane rinse
- Raw water mixing line

CONNECTION PORT SIZES:

Influent water	G 1½"
Permeate	G 1"
Concentrate	G 1½"
CIP inlet	G 1½"
CIP return	G 1½"
CIP permeate	G ½"
Antiscalant dosing port	G ½"

PHYSICAL PARAMETERS:

Approximate dimensions (bare)	2.90 × 1.20 × 1.95 m (Width × Depth × Height, ±5%)
Approximate dimensions (crated)	3.05 × 1.37 × 2.24 m (Width × Depth × Height, ±5%)
Approximate weight (bare)	340 kg
Approximate weight (crated)	500 kg

ECOSOFT MO4 8" REVERSE OSMOSIS SYSTEM

Code	Product	Flow capacity, m³/h (GPH)	Membranes**
MO4TP5	Ecosoft MO4 RO System	4–5 (1 060–1 320)	4/80 x 40

** Membranes are not included


TECHNICAL SPECIFICATION

Permeate capacity ¹	4 m³/h
Permeate recovery ²	75%
Maximum TDS	3000 mg/L
Influent flow demand	5.5...8 m³/h (service) 10 m³/h (rinse)
Operating pressure	8...12 bar
Maximum pressure	14 bar
Electrical requirements	380...400 V, 50 Hz (3 ph)
Electrical power	4 kW
Pre-filter rating	5 µm

¹ depends on feed water TDS, temperature, and permeate recovery
— see graph on the right

² for low scaling/fouling water

ECOSOFT MO4 RO FLOW CAPACITY GRAPH (WITH XLE-440 MEMBRANES)



Permeate flow rates are calculated under the following conditions:
 • 2 bar influent water pressure
 • 0 bar backpressure in the permeate line
 • fresh membranes
 • XLE-440 membrane

PIPES AND INSTRUMENTS DIAGRAM

